

PR3-BSC1/3X21 - Relay base



2833615

<https://www.phoenixcontact.com/us/products/2833615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Relay base PR3..., for REL-OR octal relays with 3 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Your advantages

- Relay base family for assembly with a 2- or 3-changeover contact relay

Commercial data

Item number	2833615
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C463
Product key	DK6314
GTIN	4017918933838
Weight per piece (including packing)	72.02 g
Weight per piece (excluding packing)	65.6 g
Customs tariff number	85366990
Country of origin	CN

PR3-BSC1/3X21 - Relay base



2833615

<https://www.phoenixcontact.com/us/products/2833615>

Technical data

Product properties

Product type	Relay socket
--------------	--------------

Electrical properties

Nominal voltage U_N	400 V AC/DC
Nominal current I_N	10 A

Connection data

Input side

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section AWG	26 ... 14 26 ... 14 (2 conductors with the same cross-section)

Output side

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ² 0.2 mm ² ... 2.5 mm ² (2 conductors with the same cross-section)
Conductor cross-section AWG	26 ... 14 26 ... 14 (2 conductors with the same cross-section)

Dimensions

Width	38 mm
Height	75 mm
Depth Retaining bracket	84 mm (EL3-M52)

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

PR3-BSC1/3X21 - Relay base



2833615

<https://www.phoenixcontact.com/us/products/2833615>

Ambient temperature (storage/transport)	-40 °C ... 85 °C
---	------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

PR3-BSC1/3X21 - Relay base

2833615

<https://www.phoenixcontact.com/us/products/2833615>



Classifications

UNSPSC

UNSPSC 21.0	39122335
-------------	----------

PR3-BSC1/3X21 - Relay base



2833615

<https://www.phoenixcontact.com/us/products/2833615>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com