

# PC WORX 3 BASIC-PRO LIC - Programming software



2812225

<https://www.phoenixcontact.com/us/products/2812225>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Upgrade of existing basic license to full license



## Your advantages

- Integrated simulation environment
- Comprehensive diagnostic possibilities such as breakpoints, individual steps, debugging in libraries, instance debugging
- Fast startup and programming, thanks to comprehensive standard libraries
- Uniform operation worldwide, thanks to programming according to IEC 61131
- A programming environment for all controllers from Phoenix Contact
- Integrated diagnostics and monitoring
- Application-specific expansion with corresponding functional blocks
- Integrated fieldbus and network configuration

## Commercial data

Item number	2812225
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DRDBAC
GTIN	4017918909635
Weight per piece (including packing)	468 g
Weight per piece (excluding packing)	468 g
Customs tariff number	85234910
Country of origin	DE

2812225

<https://www.phoenixcontact.com/us/products/2812225>

## Technical data

### Product properties

Product type	Programming
--------------	-------------

### System properties

Control system	(Target system) Field controllers, Remote Field Controllers
Intended use for the software	License programming

### Functionality

Basic functions	Function block diagram (FBD)
	Instruction list (IL)
	Structured text (ST)
	Ladder diagram (LD)
	Symbolic flowchart (SFC)
	Configuration of INTERBUS networks
	Parameterizing the INTERBUS devices
	Diagnostics for INTERBUS networks
Expanded functionality	Unlimited number of input/output data
Integrated function	Analysis
	Evaluation
	Data acquisition
	Programming
	Configuration
	Diagnostics
	Maintenance
Programming languages supported	Communication
	Programming in acc. with IEC 61131-3
	Instruction list (IL)
	Function block diagram (FBD)
	Ladder diagram (LD)
	Structured text (ST)
Configuration	Symbolic flowchart (SFC)
	INTERBUS
Diagnostics	INTERBUS
Control system	(Target system) Field controllers, Remote Field Controllers
Associated hardware	Phoenix Contact control

### System requirements

Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Spanish

2812225

<https://www.phoenixcontact.com/us/products/2812225>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)