

MPB 18/1- 5 - Wiring bridge

2817864

<https://www.phoenixcontact.com/us/products/2817864>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 5-pos.



Your advantages

- In combination with other devices in the distribution board, such as residual current devices and miniature circuit breakers
- Practical wiring of all common applications
- For combinations of lightning and surge arresters

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2817864 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL18 |
| Product key | CL132Z |
| GTIN | 4017918148201 |
| Weight per piece (including packing) | 24.23 g |
| Weight per piece (excluding packing) | 23.79 g |
| Customs tariff number | 85369095 |
| Country of origin | DE |

MPB 18/1- 5 - Wiring bridge

2817864

<https://www.phoenixcontact.com/us/products/2817864>



Technical data

Product properties

| | |
|---------------------|-------------|
| Product type | Bridge |
| Type | Comb bridge |
| Number of positions | 5 |

Electrical properties

| | |
|-----------------------|-------|
| Number of phases | 1 |
| Nominal current I_N | 100 A |

Dimensions

| | |
|--------|---------|
| Height | 90.8 mm |
|--------|---------|

Material specifications

| | |
|------------------|-----------------|
| Color | gray (RAL 7042) |
| | copper color |
| Housing material | Plastic |

MPB 18/1- 5 - Wiring bridge

2817864

<https://www.phoenixcontact.com/us/products/2817864>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371306 |
| ECLASS-15.0 | 27371306 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000215 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

MPB 18/1- 5 - Wiring bridge



2817864

<https://www.phoenixcontact.com/us/products/2817864>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com