

ME B-KA - Cover

2854173

<https://www.phoenixcontact.com/us/products/2854173>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal cover, 1 strip covers up to 12 terminal points, for ME-BUS terminal opening, (male side)



Your advantages

- Easy, tool-free mounting
- Flammability rating V0 in accordance with UL 94

Commercial data

Item number	2854173
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AC08
Product key	ACHACZ
GTIN	4017918190217
Weight per piece (including packing)	0.995 g
Weight per piece (excluding packing)	0.675 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Product properties

Product type	Filler plug
Housing type	DIN rail housing
Housing series	ME
Ventilation openings present	no

Dimensions

Width	10.8 mm
Height	51.22 mm
Depth	6 mm

Material specifications

Color (Filler plug)	green (RAL 6021)
Material Filler plug	PA
Flammability rating according to UL 94	V0
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

Mounting

Mounting type	Snap in
---------------	---------

ME B-KA - Cover

2854173

<https://www.phoenixcontact.com/us/products/2854173>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2854173>



UL Recognized

Approval ID: E240868

Classifications

ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

ME B-KA - Cover



2854173

<https://www.phoenixcontact.com/us/products/2854173>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com