

ME MAX 17,5 PLATE FRBK - Insertion plate



2896746

<https://www.phoenixcontact.com/us/products/2896746>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Insertion plate, width: 14.2 mm, height: 73.6 mm, depth: 1 mm, color: gray brown (similar RAL 8019)



Figure shows one version

Your advantages

- Easy, tool-free mounting
- Plastic in accordance with UL94 V0: for more rigorous flammability requirements

Commercial data

Item number	2896746
Packing unit	10 pc
Minimum order quantity	250 pc
Note	Made to order (non-returnable)
Product key	ACHABZ
GTIN	4046356148771
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.244 g
Country of origin	DE

ME MAX 17,5 PLATE FRBK - Insertion plate



2896746

<https://www.phoenixcontact.com/us/products/2896746>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
---------------	---

Product properties

Product type	Cover
Housing type	DIN rail housing
Housing series	ME-MAX
Ventilation openings present	no

Dimensions

Width	14.2 mm
Height	73.6 mm
Depth	1 mm

Material specifications

Color (Housing)	gray brown (RAL 8019)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA
Surface characteristics	untreated

Mounting

Mounting type	Slot
---------------	------

ME MAX 17,5 PLATE FRBK - Insertion plate



2896746

<https://www.phoenixcontact.com/us/products/2896746>

Classifications

ECLASS

ECLASS-13.0

27190605

UNSPSC

UNSPSC 21.0

31261500

ME MAX 17,5 PLATE FRBK - Insertion plate



2896746

<https://www.phoenixcontact.com/us/products/2896746>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com