

HBUS-B-L BK - Protective cap

2896843

<https://www.phoenixcontact.com/us/products/2896843>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover cap for DIN rail connector, left, width: 7.4 mm, height: 23.3 mm, color: black (similar RAL 9005)

The figure shows the standard item

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2896843 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Product key | ACHBBZ |
| GTIN | 4046356515887 |
| Weight per piece (including packing) | 0.824 g |
| Weight per piece (excluding packing) | 0.824 g |
| Country of origin | CN |

HBUS-B-L BK - Protective cap



2896843

<https://www.phoenixcontact.com/us/products/2896843>

Technical data

Product properties

| | |
|------------------------------|----------------------------------|
| Product type | Filler plug |
| Housing type | Cover cap for DIN rail connector |
| Housing series | BC |
| Ventilation openings present | no |

Dimensions

| | |
|--------|---------|
| Width | 7.4 mm |
| Height | 23.3 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
| Relative humidity (storage/transport) | 80 % |

HBUS-B-L BK - Protective cap

2896843

<https://www.phoenixcontact.com/us/products/2896843>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HBUS-B-L BK - Protective cap



2896843

<https://www.phoenixcontact.com/us/products/2896843>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com