

EMD-SL-PS-230AC - Power module



2866129

<https://www.phoenixcontact.com/us/products/2866129>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Power modules, pluggable, for EMD-SL-..., supply voltage: 195...264 V AC



Your advantages

- Adjustable via potentiometer on the front
- Variable supply voltage range
- Separately adjustable startup and response delays

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2866129 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C440 |
| Product key | DK663Z |
| GTIN | 4017918952693 |
| Weight per piece (including packing) | 50.3 g |
| Weight per piece (excluding packing) | 47.1 g |
| Customs tariff number | 85043180 |
| Country of origin | DE |

EMD-SL-PS-230AC - Power module



2866129

<https://www.phoenixcontact.com/us/products/2866129>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | Power module |
|--------------|--------------|

Input data

| | |
|------------------------|-----------------------|
| Input voltage | 230 V AC (50/60 Hz) |
| Input voltage range AC | 195 V AC ... 264 V AC |

Dimensions

| | |
|------------------|----------|
| Width | 32 mm |
| Height | 35 mm |
| Depth | 16 mm |
| Horizontal pitch | 1.8 Div. |

Material specifications

| | |
|------------------|---------|
| Housing material | Plastic |
|------------------|---------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -25 °C ... 55 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |

EMD-SL-PS-230AC - Power module



2866129

<https://www.phoenixcontact.com/us/products/2866129>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371392 |
| ECLASS-15.0 | 27371392 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002886 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

EMD-SL-PS-230AC - Power module



2866129

<https://www.phoenixcontact.com/us/products/2866129>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com