

# UEGH-BE-MT KPL BK - Electronics housing



2901288

<https://www.phoenixcontact.com/us/products/2901288>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Base element with integrated connection technology, color: black (similar RAL 9005)

## Commercial data

Item number	2901288
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCCZ
GTIN	4046356139717
Weight per piece (including packing)	34.03 g
Weight per piece (excluding packing)	28.97 g
Customs tariff number	85369010
Country of origin	DE

2901288

<https://www.phoenixcontact.com/us/products/2901288>

## Technical data

### Product properties

Product type	Lower housing part
Housing type	Component housing
Housing series	UEG
Product family	UEGH

### Material specifications

Color (Housing)	black (RAL 9005)
Material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C

# UEGH-BE-MT KPL BK - Electronics housing



2901288

<https://www.phoenixcontact.com/us/products/2901288>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901288>



**UL Recognized**

Approval ID: E240868

2901288

<https://www.phoenixcontact.com/us/products/2901288>

## Classifications

### ECLASS

ECLASS-13.0	27190401
ECLASS-15.0	27190401

### ETIM

ETIM 9.0	EC001031
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

2901288

<https://www.phoenixcontact.com/us/products/2901288>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)