


# EG 90-AE/ABS GN S88 - Upper housing part

2890373

<https://www.phoenixcontact.com/us/products/2890373>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Housing cover, for connection on one side



The figure shows a version of the product

## Commercial data

Item number	2890373
Packing unit	10 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Product key	ACHCGA
GTIN	4046356092661
Weight per piece (including packing)	23.09 g
Weight per piece (excluding packing)	16.748 g
Country of origin	DE

# EG 90-AE/ABS GN S88 - Upper housing part



2890373

<https://www.phoenixcontact.com/us/products/2890373>

## Technical data

### Product properties

Product type	Upper housing part
Housing type	Component housing
Housing series	EG
Product family	EG...A
Ventilation openings present	no

### Dimensions

Width	90 mm
Height	75 mm

### Material specifications

Color	green (RAL 6021)
Material	ABS
Flammability rating according to UL 94	HB

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C

### Mounting

Mounting type	Snap in
---------------	---------

# EG 90-AE/ABS GN S88 - Upper housing part



2890373

<https://www.phoenixcontact.com/us/products/2890373>

## Classifications

### ECLASS

ECLASS-13.0

27190603

### UNSPSC

UNSPSC 21.0

31261500

# EG 90-AE/ABS GN S88 - Upper housing part



2890373

<https://www.phoenixcontact.com/us/products/2890373>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)