

FL DIN RA - DIN rail adapter



2891053

<https://www.phoenixcontact.com/us/products/2891053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.



Product description

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted

Your advantages

- Rugged: 17.5 kg weight capacity, allows mounting large quantity and types of devices
- Rugged: Secure depth detents maintain “no –slip” depth settings
- Flexible: Ten adjustable depth settings (20 mm increments, 70 to 210 mm depth,) allows easy front access to all equipment types
- Easy and secure adapting of DIN rail products to industrial racks

Commercial data

Item number	2891053
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN22
Product key	DNN1ZZ
GTIN	4055626047775
Weight per piece (including packing)	1,770 g
Weight per piece (excluding packing)	1,767 g
Customs tariff number	73269098
Country of origin	TW

FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/us/products/2891053>



Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	DIN rail adapter
--------------	------------------

Dimensions

Width	464 mm
Height	105 mm
Depth	285 mm

Material specifications

Color	white aluminium (RAL 9006)
Material	Steel, chrome-plated
Material	Steel, chrome-plated

FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/us/products/2891053>



Classifications

ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

ETIM

ETIM 10.0	EC001024
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FL DIN RA - DIN rail adapter



2891053

<https://www.phoenixcontact.com/us/products/2891053>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com