


VF-SI/TR5/0,063AT - Fuse set



2901004

<https://www.phoenixcontact.com/us/products/2901004>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse set, number: 8 Pcs., fuse type: Fuse (TR5), nominal current: 0.063 A, tripping characteristic: slow-blow (T)

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2901004 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK218Z |
| GTIN | 4046356557177 |
| Weight per piece (including packing) | 5.8 g |
| Weight per piece (excluding packing) | 0.57 g |
| Customs tariff number | 85361010 |
| Country of origin | DE |

VF-SI/TR5/0,063AT - Fuse set



2901004

<https://www.phoenixcontact.com/us/products/2901004>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Product properties

| | |
|----------------------------|------|
| Product type | Fuse |
| Number of fuses in the set | 8 |

Electrical properties

| | |
|---|---------------|
| Tripping characteristic | slow-blow (T) |
| Maximum power dissipation for nominal condition | 0.2 W |
| Nominal voltage U_N | 250 V |
| Nominal current I_N | 0.063 A |
| Fuse rating | TR5 |
| Fuse | Fuse |

Dimensions

| | |
|------------|------------|
| Dimensions | 8.5 x 8 mm |
|------------|------------|

VF-SI/TR5/0,063AT - Fuse set



2901004

<https://www.phoenixcontact.com/us/products/2901004>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901004>



EAC

Approval ID: RU C-DE.BL08.B.00724

VF-SI/TR5/0,063AT - Fuse set



2901004

<https://www.phoenixcontact.com/us/products/2901004>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27142002 |
| ECLASS-15.0 | 27142002 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002704 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

VF-SI/TR5/0,063AT - Fuse set



2901004

<https://www.phoenixcontact.com/us/products/2901004>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com