

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/us/products/2901699>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Cover, width: 45.2 mm, height: 75.25 mm, depth: 5.5 mm, color: transparent



The figure shows a version of the product

## Your advantages

- Easy, tool-free mounting

## Commercial data

Item number	2901699
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC08
Product key	ACHABZ
GTIN	4046356150408
Weight per piece (including packing)	8.23 g
Weight per piece (excluding packing)	6.29 g
Customs tariff number	85389099
Country of origin	DE

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/us/products/2901699>

## Technical data

### Notes

Assembly note	Please observe the application note in the download area.
---------------	-----------------------------------------------------------

### Product properties

Product type	Cover
Housing type	DIN rail housing
Housing type	Modular housings
Housing series	ME-MAX
Product family	ME MAX 45..
Ventilation openings present	no

### Dimensions

Width	45.2 mm
Height	75.25 mm
Depth	5.5 mm

### Material specifications

Color (Housing cover)	transparent
Material	PC
Flammability rating according to UL 94	V2
CTI according to IEC 60112	250

### PCB data

Type of PCB mount	Latching
-------------------	----------

### Mounting

Mounting type	Latching with lower housing part
---------------	----------------------------------

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/us/products/2901699>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2901699>



**UL Recognized**

Approval ID: E240868

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/us/products/2901699>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# ME MAX 45 DKL TRANS - Housing cover



2901699

<https://www.phoenixcontact.com/us/products/2901699>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.058 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)