

# UEGM 40/2 BEIGE SO 5 - Electronics housing



2906542

<https://www.phoenixcontact.com/us/products/2906542>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronics housing, color: beige ,Component housing, without vents, Complete housing, cross connection: Not provided for

## Commercial data

Item number	2906542
Packing unit	8 pc
Minimum order quantity	8 pc
Note	Made to order (non-returnable)
Product key	ACHCCB
GTIN	4017918244446
Weight per piece (including packing)	71.8 g
Weight per piece (excluding packing)	52.925 g
Country of origin	DE

2906542

<https://www.phoenixcontact.com/us/products/2906542>

## Technical data

### Product properties

Product type	Complete housing
Housing type	Component housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM 40
Number of positions	12
Ventilation openings present	no

### Material specifications

Color (Housing)	beige (RAL 7032)
-----------------	------------------

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# UEGM 40/2 BEIGE SO 5 - Electronics housing




2906542

<https://www.phoenixcontact.com/us/products/2906542>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906542>

 <b>cULus Recognized</b> Approval ID: E60425-19770427				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	300 V	10 A	30 - 12	-

2906542

<https://www.phoenixcontact.com/us/products/2906542>

## Classifications

### ECLASS

ECLASS-13.0	27190501
ECLASS-15.0	27190501

### ETIM

ETIM 10.0	EC001031
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UEGM 40/2 BEIGE SO 5 - Electronics housing



2906542

<https://www.phoenixcontact.com/us/products/2906542>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.588 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)