

# CABLE- 9/8/250/RSM/ELAU - Adapter cable



2902984

<https://www.phoenixcontact.com/us/products/2902984>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable adapter for PSR over-speed safety relays (PSR-RSM4 and PSR-MM30), 9/8-pos., cable length: 2.5 m, for controller: ELAU



The figure shows a comparable item from Phoenix Contact

## Commercial data

Item number	2902984
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNA24Z
GTIN	4046356701938
Weight per piece (including packing)	158 g
Weight per piece (excluding packing)	155.9 g
Country of origin	DE

# CABLE- 9/8/250/RSM/ELAU - Adapter cable



2902984

<https://www.phoenixcontact.com/us/products/2902984>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Adapter cable
--------------	---------------

### Connection data

#### To the device

Connection method	RJ45
Number of positions	8

#### Encoder / PLC

Connection method	D-SUB 9 plug/D-SUB 9 socket
Number of positions	9

### Material specifications

Outer sheath, material	LSHF (FRNC)
Conductor material	Bare Cu litz wires

### Cable/line

Cable length	2.5 m
Outer sheath, material	LSHF (FRNC)
Cable cross section	0.48 mm <sup>2</sup> (AWG 26)
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield Soldering on D-SUB housing
Cable resistance	≤ 260 Ω/km

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation)
	0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

# CABLE- 9/8/250/RSM/ELAU - Adapter cable



2902984

<https://www.phoenixcontact.com/us/products/2902984>

## Classifications

### ECLASS

ECLASS-13.0

27371390

### ETIM

ETIM 9.0

EC002498

### UNSPSC

UNSPSC 21.0

26121600

# CABLE- 9/8/250/RSM/ELAU - Adapter cable



2902984

<https://www.phoenixcontact.com/us/products/2902984>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)