


# VF-SI/TR5/0,25AF - Fuse set

2903435

<https://www.phoenixcontact.com/us/products/2903435>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse set, number: 8 Pcs., fuse type: Fuse (TR5), nominal current: 0.25 A, tripping characteristic: fast-blow (F)

## Commercial data

Item number	2903435
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK218Z
GTIN	4046356738347
Weight per piece (including packing)	6 g
Weight per piece (excluding packing)	6 g
Country of origin	CN

# VF-SI/TR5/0,25AF - Fuse set



2903435

<https://www.phoenixcontact.com/us/products/2903435>

## Technical data

### Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

### Product properties

Product type	Fuse
Number of fuses in the set	8

### Electrical properties

Tripping characteristic	fast-blow (F)
Maximum power dissipation for nominal condition	0.25 W
Nominal voltage $U_N$	250 V
Nominal current $I_N$	0.25 A
Fuse rating	TR5
Fuse	Fuse

### Dimensions

Dimensions	8.5 x 8 mm
------------	------------

# VF-SI/TR5/0,25AF - Fuse set

2903435

<https://www.phoenixcontact.com/us/products/2903435>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903435>



**EAC**

Approval ID: RU C-DE.BL08.B.00724

# VF-SI/TR5/0,25AF - Fuse set



2903435

<https://www.phoenixcontact.com/us/products/2903435>

## Classifications

### ECLASS

ECLASS-13.0	27142002
ECLASS-15.0	27142002

### ETIM

ETIM 9.0	EC002704
----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# VF-SI/TR5/0,25AF - Fuse set



2903435

<https://www.phoenixcontact.com/us/products/2903435>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)