

# SAMPLE BAG ME 22,5 - Electronics housing



2907282

<https://www.phoenixcontact.com/us/products/2907282>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, width: 22.6 mm, height: 99 mm, depth: 45.85 mm, color: green (similar RAL 6021)

## Commercial data

Item number	2907282
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AC08
Product key	ACHAAA
GTIN	4017918349325
Weight per piece (including packing)	316 g
Weight per piece (excluding packing)	249.34 g
Customs tariff number	85369010
Country of origin	DE

2907282

<https://www.phoenixcontact.com/us/products/2907282>

## Technical data

### Product properties

Product type	Lower housing part
Housing type	DIN rail housing
Housing series	ME

### Dimensions

Width	22.6 mm
Height	99 mm
Depth	45.85 mm
Depth from base support surface	38.5 mm

### PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

### Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V0
CTI according to IEC 60112	600
Housing material	PA

### Environmental and real-life conditions

#### Ambient conditions

Max. IP code to attain	IP20
------------------------	------

### PCB data

Type of PCB mount	Latching
Thickness of the PCB	1.4 mm ... 1.8 mm

### Mounting

Mounting type	Latching with lower housing part
---------------	----------------------------------

# SAMPLE BAG ME 22,5 - Electronics housing

2907282

<https://www.phoenixcontact.com/us/products/2907282>



## Classifications

### ECLASS

ECLASS-15.0

27190601

### UNSPSC

UNSPSC 21.0

31261501

# SAMPLE BAG ME 22,5 - Electronics housing



2907282

<https://www.phoenixcontact.com/us/products/2907282>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)