UPS-BAT-KIT-WTR 2X12V/26AH - Uninterruptible power supply replacement battery

2908369

https://www.phoenixcontact.com/us/products/2908369

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-BAT/VRLA-WTR... battery modules



Commercial data

Item number	2908369
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM24
Product key	CMUEW3
GTIN	4055626297736
Weight per piece (including packing)	20,000 g
Weight per piece (excluding packing)	20,000 g
Customs tariff number	85072080
Country of origin	US

Technical data

Notes

General

Note on the battery	This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under “Latest startup”.

Input data

Input voltage	2x 12 V DC

Energy storage

Nominal capacity	26 Ah
Battery module service life	10 Years ... 15 Years (20 °C)
Latest startup date (battery only)	12 Months (0 °C ... 20 °C)
Latest startup (battery only) - range	9 Months ... 12 Months (20 °C ... 30 °C)
	6 Months ... 9 Months (30 °C ... 40 °C)
Battery technology	VRLA-WTR
Accumulator type	Genesis G26EPX
IQ technology	no

Product properties

Product type	Battery
Product family	Replacement battery
Application	for UPS-BAT/VRLA/WTR
IQ technology	no

Dimensions

Width	352 mm
Height	126 mm
Depth	167 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 60 °C
Max. permissible relative humidity (operation)	≤ 95 %

Ex data

Suited for EX-applications	no

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2908369

GOST-R
Approval ID: ROSS DE.BL08.D00191

Classifications

ECLASS

ECLASS-13.0	27059090
ECLASS-15.0	27050492

ETIM

ETIM 10.0	EC002839

UNSPSC

UNSPSC 21.0	26111700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	19905a6b-eda9-42e7-adfb-98b2e75a496c

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com