

FASTCON PRO-SET - Connector set



2906227

<https://www.phoenixcontact.com/us/products/2906227>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FASTCON Pro plug set consisting of four plugs with screw connection, one for each position on the module. Suitable for all MINI Analog Pro modules.

Product description

FASTCON Pro plug set consisting of four plugs, one for each position on the module. Suitable for all MINI Analog Pro modules. The plugs can easily replace the existing plugs, for example, to change the connection technology. As such, lost plugs can be replaced. Four-way coding prevents incorrect insertion into the device.

Commercial data

Item number	2906227
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C499
Product key	DK112Z
GTIN	4055626047935
Weight per piece (including packing)	28.6 g
Weight per piece (excluding packing)	20.8 g
Customs tariff number	85366990
Country of origin	DE

FASTCON PRO-SET - Connector set



2906227

<https://www.phoenixcontact.com/us/products/2906227>

Technical data

Product properties

Product type	Connector set
--------------	---------------

Connection data

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ² (with ferrule)
	0.2 mm ² ... 2.5 mm ² (without ferrule)
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 12
	24 ... 12 (flexible)

FASTCON PRO-SET - Connector set



2906227

<https://www.phoenixcontact.com/us/products/2906227>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

FASTCON PRO-SET - Connector set



2906227

<https://www.phoenixcontact.com/us/products/2906227>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com