

UMK-SE 11,25-1 O.LOGO - Lateral element



2906351

<https://www.phoenixcontact.com/us/products/2906351>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Lateral element, profile width (internal): 72.2 mm, profile width (external): 77 mm, length: 11.25 mm



Commercial data

Item number	2906351
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	NULL
Product key	ACHDCA
GTIN	4017918277499
Weight per piece (including packing)	5.63 g
Weight per piece (excluding packing)	5.55 g
Customs tariff number	85389099
Country of origin	PL

UMK-SE 11,25-1 O.LOGO - Lateral element



2906351

<https://www.phoenixcontact.com/us/products/2906351>

Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UMK
Product family	UMK SE
Ventilation openings present	no

Dimensions

Length	11.25 mm
--------	----------

External dimensions

Profile width (external)	77 mm
--------------------------	-------

Internal dimensions

Profile width (internal)	72.2 mm
--------------------------	---------

Material specifications

Color (Housing)	green (RAL 6021)
Material	PA
Flammability rating according to UL 94	V2
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

UMK-SE 11,25-1 O.LOGO - Lateral element



2906351

<https://www.phoenixcontact.com/us/products/2906351>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UMK-SE 11,25-1 O.LOGO - Lateral element



2906351

<https://www.phoenixcontact.com/us/products/2906351>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com