

BRIDGE- 4- 2M/0,3M - Bridge

2909899

<https://www.phoenixcontact.com/us/products/2909899>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

3-phase loop bridge for 4 CONTACTRON modules, with screw connection and 22.5 mm housing width, cable length between the modules: 0.3 m, connecting cable: 2 m



Your advantages

- Bridging of 2 to 10 devices with maximum module spacing of 22.5 mm
- Bridging of 2 to 10 devices with maximum module spacing of 22.5 mm
- Up to 575 V AC/3 x 25 A

Commercial data

Item number	2909899
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C470
Product key	DK74Z1
GTIN	4055626408316
Weight per piece (including packing)	308.8 g
Weight per piece (excluding packing)	287.8 g
Customs tariff number	85444290
Country of origin	DE

BRIDGE- 4- 2M/0,3M - Bridge

2909899

<https://www.phoenixcontact.com/us/products/2909899>



Technical data

Product properties

Product type	Loop bridge
Product family	CONTACTRON
Number of bridgeable modules	4

Electrical properties

Operating voltage range	42 V AC ... 575 V AC
Operating current	≤ 25 A

Dimensions

Width	22.5 mm
-------	---------

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Cable/line

Connecting cable length	2 m
Cable cross section	2.5 mm ²

BRIDGE- 4- 2M/0,3M - Bridge

2909899

<https://www.phoenixcontact.com/us/products/2909899>



Drawings



Figure shows the version BRIDGE- 4

BRIDGE- 4- 2M/0,3M - Bridge

2909899

<https://www.phoenixcontact.com/us/products/2909899>



Classifications

ECLASS

ECLASS-13.0

27371392

ETIM

ETIM 9.0

EC002498

UNSPSC

UNSPSC 21.0

39121100

BRIDGE- 4- 2M/0,3M - Bridge



2909899

<https://www.phoenixcontact.com/us/products/2909899>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com