

# TMC 8 B3 80 48 CA - Wiring bridge

2907997

<https://www.phoenixcontact.com/us/products/2907997>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Image shows ...C version

Bus bar for TMC 83... circuit breakers (three phase) with auxilliary switch. 17.8 mm pitch, up to 48 positions. Rated for 80 A (end feed) 600 V AC/DC. UL 508 Listed for connection of UL 489 rated circuit breakers.

## Commercial data

Item number	2907997
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CL08
Product key	CLA125
GTIN	4055626352930
Weight per piece (including packing)	393 g
Weight per piece (excluding packing)	393 g
Customs tariff number	85362010
Country of origin	DE

# TMC 8 B3 80 48 CA - Wiring bridge

2907997

<https://www.phoenixcontact.com/us/products/2907997>

## Technical data


### Product properties

Product type	Bridge
Type	Comb bridge
Number of positions	48

### Electrical properties

Number of phases	3
Rated voltage (III/3)	600 V
Nominal voltage $U_N$	600 V AC/DC
Nominal current $I_N$	80 A (End feed) 160 A (Center feed with two 115A TMC 8 B TERM PIN terminals required per phase)

### Dimensions

Dimensional drawing	
Width	1006 mm
Height	19.3 mm
Depth	59.2 mm

### Material specifications

Color	light gray (RAL 7035)
Housing material	Plastic

# TMC 8 B3 80 48 CA - Wiring bridge


2907997

<https://www.phoenixcontact.com/us/products/2907997>



## Drawings

Dimensional drawing



# TMC 8 B3 80 48 CA - Wiring bridge



2907997

<https://www.phoenixcontact.com/us/products/2907997>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2907997>



**UL Listed**

Approval ID: E123528



**cUL Listed**

Approval ID: E123528

# TMC 8 B3 80 48 CA - Wiring bridge



2907997

<https://www.phoenixcontact.com/us/products/2907997>

## Classifications

### ECLASS

ECLASS-13.0	27371306
ECLASS-15.0	27371306

### ETIM

ETIM 10.0	EC000215
-----------	----------

# TMC 8 B3 80 48 CA - Wiring bridge



2907997

<https://www.phoenixcontact.com/us/products/2907997>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	10.292 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)