

MINI-SCREW-USB-DATACABLE - Data cable



2908217

<https://www.phoenixcontact.com/us/products/2908217>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Used for communication between an industrial PC and Phoenix Contact devices with USB-Mini-B connection.

Product description

Data cable for communication between higher-level controllers and uninterruptible power supply units.

Commercial data

Item number	2908217
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM20
Product key	CMU2Z9
GTIN	4055626288741
Weight per piece (including packing)	113 g
Weight per piece (excluding packing)	109.1 g
Customs tariff number	85444290
Country of origin	CN

MINI-SCREW-USB-DATACABLE - Data cable



2908217

<https://www.phoenixcontact.com/us/products/2908217>

Technical data

Product properties

Product type	Data cable preassembled
Application	Communication with UPS
Sensor type	USB

Electrical properties

Transmission medium	Copper
Transmission speed	115200 bps

Connection data

PC side

Connection method	USB 2.0 Fullspeed
-------------------	-------------------

Device side

Connection method	Mini USB type B
Number of positions	5

Cable/line

Cable length	3 m
--------------	-----

MINI-SCREW-USB-DATACABLE - Data cable



2908217

<https://www.phoenixcontact.com/us/products/2908217>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908217>



EAC-RoHS

Approval ID: RU*-DE*35.B.00385/20

MINI-SCREW-USB-DATACABLE - Data cable



2908217

<https://www.phoenixcontact.com/us/products/2908217>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

ETIM

ETIM 10.0	EC003249
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

MINI-SCREW-USB-DATACABLE - Data cable



2908217

<https://www.phoenixcontact.com/us/products/2908217>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.249 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com