

VIP/U/RAIL 3L DIVIDER - Partition plate



2908555

<https://www.phoenixcontact.com/us/products/2908555>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP I/O marshalling partition plate for safe isolation between non-Ex i and Ex i assembled base modules for Honeywell systems. The partition plate is mounted directly on the DIN rail at the end of the base module.

Your advantages

- Rail mounted divider at the end of the VIP base module provides separation between circuits
- Durable, sleek design

Commercial data

Item number	2908555
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C480
Product key	DK115Z
GTIN	4055626408163
Weight per piece (including packing)	20.1 g
Weight per piece (excluding packing)	20.1 g
Customs tariff number	39269097
Country of origin	US

VIP/U/RAIL 3L DIVIDER - Partition plate



2908555

<https://www.phoenixcontact.com/us/products/2908555>

Technical data

Product properties

Product type	Partition plate
Product family	VIP I/O-Marshalling

Mounting

Mounting type	any
---------------	-----

Material specifications

Color	gray (RAL 7042)
Material	PA 6.6

Dimensions

Width	5 mm
Height	136.7 mm
Depth	88.2 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

VIP/U/RAIL 3L DIVIDER - Partition plate



2908555

<https://www.phoenixcontact.com/us/products/2908555>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

VIP/U/RAIL 3L DIVIDER - Partition plate



2908555

<https://www.phoenixcontact.com/us/products/2908555>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com