

# EG 67,5-A/ABS BEIGE S51 - Upper housing part



2909154

<https://www.phoenixcontact.com/us/products/2909154>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Upper housing part ,Component housing, length: 75 mm, Upper part, width: 67.5 mm, height: 17.5 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2909154       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 1 pc          |
| Product key                          | ACHCGA        |
| GTIN                                 | 4017918398590 |
| Weight per piece (including packing) | 16.259 g      |
| Weight per piece (excluding packing) | 11.029 g      |
| Country of origin                    | DE            |

# EG 67,5-A/ABS BEIGE S51 - Upper housing part



2909154

<https://www.phoenixcontact.com/us/products/2909154>

## Technical data

### Product properties

|                     |                    |
|---------------------|--------------------|
| Product type        | Upper housing part |
| Housing type        | Component housing  |
| Product family      | EG..-A             |
| Number of positions | 26                 |

### Dimensions

|                  |         |
|------------------|---------|
| Width            | 67.5 mm |
| Installed height | 17.5 mm |
| Depth            | 75 mm   |
| Length           | 75 mm   |

### Material specifications

|  |    |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

# EG 67,5-A/ABS BEIGE S51 - Upper housing part



2909154

<https://www.phoenixcontact.com/us/products/2909154>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# EG 67,5-A/ABS BEIGE S51 - Upper housing part



2909154

<https://www.phoenixcontact.com/us/products/2909154>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)