

# EMG 22-B4 - Electronics housing

2946146

<https://www.phoenixcontact.com/us/products/2946146>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Custom circuit module, consisting of housing, MKDS 3 connection terminal blocks and PCB



## Commercial data

Item number	2946146
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AC11
Product key	ACHCBA
GTIN	4017918082109
Weight per piece (including packing)	42.66 g
Weight per piece (excluding packing)	42.66 g
Customs tariff number	85369010
Country of origin	DE

# EMG 22-B4 - Electronics housing

2946146


<https://www.phoenixcontact.com/us/products/2946146>

## Technical data

### Product properties

Product type	Stackable housing set
Housing type	Component housing
Housing series	EMG
Product family	EMG
Type	Lower housing part, removable cover as option, connection system integrated, PCB integrated
Number of positions	8
Pitch	5 mm
Ventilation openings present	no

### Dimensions

Dimensional drawing	
Width	22.5 mm
Installed height	47.5 mm
Height NS 35/7,5	55 mm
	83 mm
	100 mm
Depth	75 mm
Length	75 mm
Pitch	5 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PC (glass-fiber reinforced)
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# EMG 22-B4 - Electronics housing

2946146

<https://www.phoenixcontact.com/us/products/2946146>



## Drawings

Dimensional drawing



1 = Top edge of the PCB


B = Housing width

# EMG 22-B4 - Electronics housing

2946146

<https://www.phoenixcontact.com/us/products/2946146>

Dimensional drawing



Pitch 5 mm

a = Area for mounting components, 38 mm in the hood

b = Area for mounting components, 45 mm in the housing

# EMG 22-B4 - Electronics housing



2946146

<https://www.phoenixcontact.com/us/products/2946146>

## Classifications

### ECLASS

ECLASS-15.0	27190301
ECLASS-13.0	27190301

### ETIM

ETIM 10.0	EC001031
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# EMG 22-B4 - Electronics housing



2946146

<https://www.phoenixcontact.com/us/products/2946146>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.593 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)