

# UM122-FE - Foot element



2909471

<https://www.phoenixcontact.com/us/products/2909471>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

UM 122 FE foot element, for UM 122 profile housing



## Commercial data

Item number	2909471
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918171674
Weight per piece (including packing)	10.4 g
Weight per piece (excluding packing)	9.7 g
Customs tariff number	39269097
Country of origin	PL

# UM122-FE - Foot element



2909471

<https://www.phoenixcontact.com/us/products/2909471>

## Technical data

### Product properties

Product type	Base latches
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM122

### Dimensions

Width	14.3 mm
Height	135.9 mm
Depth	20.95 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Flammability rating according to UL 94	V0

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# UM122-FE - Foot element



2909471

<https://www.phoenixcontact.com/us/products/2909471>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2909471>



**UL Recognized**

Approval ID: E240868

# UM122-FE - Foot element



2909471

<https://www.phoenixcontact.com/us/products/2909471>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM122-FE - Foot element



2909471

<https://www.phoenixcontact.com/us/products/2909471>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)