

UM-A/U N 73 14CM - Covering hood

2914615

<https://www.phoenixcontact.com/us/products/2914615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Cover, width: 73 mm



The figure shows the standard item

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2914615
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHDBZ
GTIN	4017918959401
Weight per piece (including packing)	41.7 g
Weight per piece (excluding packing)	39.7 g
Country of origin	DE

UM-A/U N 73 14CM - Covering hood



2914615

<https://www.phoenixcontact.com/us/products/2914615>

Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM AU N
Ventilation openings present	no

Dimensions

Width	73 mm
-------	-------

Material specifications

Color (Housing)	transparent
Material	PC
Surface characteristics	untreated

UM-A/U N 73 14CM - Covering hood



2914615

<https://www.phoenixcontact.com/us/products/2914615>

Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-A/U N 73 14CM - Covering hood



2914615

<https://www.phoenixcontact.com/us/products/2914615>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com