

# RAD-SYS-NEMA4X-SMS - Control cabinet



2917189

<https://www.phoenixcontact.com/us/products/2917189>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

NEMA 4X enclosure for SMS relay



## Product description

NEMA 4X enclosure preconfigured for wireless systems. Includes power supply and surge protection.

## Commercial data

Item number	2917189
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNC6P2
GTIN	4046356671552
Weight per piece (including packing)	4,790 g
Weight per piece (excluding packing)	4,790 g
Customs tariff number	85371090
Country of origin	CH

# RAD-SYS-NEMA4X-SMS - Control cabinet



2917189

<https://www.phoenixcontact.com/us/products/2917189>

## Set consists of

### STEP-PS/ 1AC/24DC/0.75 - Power supply

2868635

<https://www.phoenixcontact.com/us/products/2868635>




Primary-switched STEP POWER power supply for DIN rail mounting, input: 1-phase, output: 24 V DC/0.75 A

---

### PT 2-PE/S-230AC-ST - Type 3 surge protection plug

2839347

<https://www.phoenixcontact.com/us/products/2839347>



Type 3 arrester replacement plug (device protection) for 1-phase power supply networks with separate N and PE (3-conductor system: L1, N, PE).

# RAD-SYS-NEMA4X-SMS - Control cabinet



2917189

<https://www.phoenixcontact.com/us/products/2917189>

## PSI-MODEM-SMS-REL/6ADI/4DO/DC - Signaling system

2313520

<https://www.phoenixcontact.com/us/products/2313520>



SMS remote control and signaling system for mounting on EN DIN rail. Installation built-in device as per DIN 43880. 6 analog or digital configurable inputs and 4 relay outputs. Supply voltage 24 V DC. Scope of supply: SMS relay, antenna, software, RS-232 cable.

# RAD-SYS-NEMA4X-SMS - Control cabinet



2917189

<https://www.phoenixcontact.com/us/products/2917189>

## Technical data

### Product properties

Product type	Control box
--------------	-------------

### Dimensions

Width	311 mm
Height	359 mm
Depth	156 mm

### Material specifications

Housing material	Fiberglass
------------------	------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	NEMA 4X
----------------------	---------

# RAD-SYS-NEMA4X-SMS - Control cabinet



2917189

<https://www.phoenixcontact.com/us/products/2917189>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)