

EMG-KA - Cover

2941510

<https://www.phoenixcontact.com/us/products/2941510>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Terminal block/screw cover, set consisting of 50 strips each for terminal blocks and screw openings, 1 strip covers 12 terminal points.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2941510 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | AC11 |
| Product key | ACHCBZ |
| GTIN | 4017918080488 |
| Weight per piece (including packing) | 1.83 g |
| Weight per piece (excluding packing) | 1.83 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

EMG-KA - Cover

2941510

<https://www.phoenixcontact.com/us/products/2941510>



Technical data

Product properties

| | |
|----------------|-------------------|
| Product type | Filler plug |
| Housing type | Component housing |
| Housing series | EMG |
| Product family | EMG |

Material specifications

| | |
|-------------------------|------------------|
| Color (Housing) | green (RAL 6021) |
| Material Housing | PA |
| Surface characteristics | untreated |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
|---------------------------------|-------------------|

EMG-KA - Cover

2941510

<https://www.phoenixcontact.com/us/products/2941510>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

EMG-KA - Cover



2941510

<https://www.phoenixcontact.com/us/products/2941510>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com