

# UM-BEFE 35-1-NS 35 - Base element

2959065

<https://www.phoenixcontact.com/us/products/2959065>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element with snap-on foot, for mounting on NS 35/7,5 DIN rail, without ribs, L = 35 mm



Figure shows one version

## Commercial data

Item number	2959065
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHDDA
GTIN	4017918251772
Weight per piece (including packing)	22.54 g
Weight per piece (excluding packing)	20 g
Country of origin	PL

# UM-BEFE 35-1-NS 35 - Base element



2959065

<https://www.phoenixcontact.com/us/products/2959065>

## Technical data

### Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Plug-in module DIN rail-mount base
Housing series	UM
Product family	UM BE
Ventilation openings present	no

### Dimensions

Width	35 mm
Height	111 mm
Depth	27.7 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	80 %

### PCB data

Number of PCB holders	1
-----------------------	---

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# UM-BEFE 35-1-NS 35 - Base element



2959065

<https://www.phoenixcontact.com/us/products/2959065>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959065>



**UL Recognized**

Approval ID: E240868

# UM-BEFE 35-1-NS 35 - Base element



2959065

<https://www.phoenixcontact.com/us/products/2959065>

## Classifications

### ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM-BEFE 35-1-NS 35 - Base element



2959065

<https://www.phoenixcontact.com/us/products/2959065>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)