

EMG 22-H 7,5MM KLAR - Covering hood



2946159

<https://www.phoenixcontact.com/us/products/2946159>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm, width: 22.5 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2946159 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC11 |
| Product key | ACHCBA |
| GTIN | 4017918082116 |
| Weight per piece (including packing) | 3.36 g |
| Weight per piece (excluding packing) | 3.3 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

EMG 22-H 7,5MM KLAR - Covering hood



2946159

<https://www.phoenixcontact.com/us/products/2946159>

Technical data

Product properties

| | |
|------------------------------|-------------------|
| Product type | Cover |
| Housing type | Component housing |
| Housing series | EMG |
| Product family | EMG |
| Number of positions | 8 |
| Ventilation openings present | no |

Dimensions

| | |
|--------|---------|
| Width | 22.5 mm |
| Depth | 75 mm |
| Length | 38 mm |

Material specifications

| | |
|--|-------------|
| Color (Housing) | transparent |
| Material | PC |
| Flammability rating according to UL 94 | V2 |
| Surface characteristics | untreated |

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

EMG 22-H 7,5MM KLAR - Covering hood



2946159

<https://www.phoenixcontact.com/us/products/2946159>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190603 |
| ECLASS-15.0 | 27190603 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

EMG 22-H 7,5MM KLAR - Covering hood



2946159

<https://www.phoenixcontact.com/us/products/2946159>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.071 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com