

# UM 72-LG 10 - Lateral element



2959366

<https://www.phoenixcontact.com/us/products/2959366>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile housing and board base, 10 mm wide module, consisting of two side elements



## Commercial data

Item number	2959366
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918117603
Weight per piece (including packing)	13.944 g
Weight per piece (excluding packing)	13.76 g
Customs tariff number	39269097
Country of origin	PL

# UM 72-LG 10 - Lateral element

2959366


<https://www.phoenixcontact.com/us/products/2959366>

## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM72
Type	For PCB dimensions: 8 mm x 72 mm

### Dimensions

Dimensional drawing	
Width	8 mm
Depth	89.6 mm
Length	72 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

### PCB data

Number of PCB holders	2
-----------------------	---

### Mounting

Mounting type	DIN rail mounting, screw connection with extruded profile
---------------	---

# UM 72-LG 10 - Lateral element


2959366

<https://www.phoenixcontact.com/us/products/2959366>



## Drawings

Dimensional drawing



# UM 72-LG 10 - Lateral element



2959366

<https://www.phoenixcontact.com/us/products/2959366>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959366>



**UL Recognized**

Approval ID: E240868

# UM 72-LG 10 - Lateral element



2959366

<https://www.phoenixcontact.com/us/products/2959366>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UM 72-LG 10 - Lateral element



2959366

<https://www.phoenixcontact.com/us/products/2959366>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.072 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)