

EMG 30-H 15MM KLAR - Covering hood

2947899

<https://www.phoenixcontact.com/us/products/2947899>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 30 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2947899 |
| Packing unit | 5 pc |
| Minimum order quantity | 5 pc |
| Sales key | AC11 |
| Product key | ACHCBA |
| GTIN | 4017918083007 |
| Weight per piece (including packing) | 7.46 g |
| Weight per piece (excluding packing) | 7.46 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

EMG 30-H 15MM KLAR - Covering hood



2947899

<https://www.phoenixcontact.com/us/products/2947899>

Technical data

Product properties

| | |
|------------------------------|-------------------|
| Product type | Cover |
| Housing type | Component housing |
| Housing series | EMG |
| Product family | EMG |
| Number of positions | 10 |
| Ventilation openings present | no |

Dimensions

| | |
|--------|-------|
| Width | 30 mm |
| Depth | 75 mm |
| Length | 38 mm |

Material specifications

| | |
|--|-------------|
| Color (Housing) | transparent |
| Material | PC |
| Flammability rating according to UL 94 | V2 |
| Surface characteristics | untreated |

Mounting

| | |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

EMG 30-H 15MM KLAR - Covering hood



2947899

<https://www.phoenixcontact.com/us/products/2947899>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190603 |
| ECLASS-15.0 | 27190603 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

EMG 30-H 15MM KLAR - Covering hood



2947899

<https://www.phoenixcontact.com/us/products/2947899>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com