

EMG 45-RELS/K2-W230 - Relay base

2950802

<https://www.phoenixcontact.com/us/products/2950802>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module with plug-in base for KAMMRELAIS® size 2, contact: B 110, 4 changeover contacts, input voltage 120-230 V AC, with LED display, freewheeling and polarity protection diode

The figure shows version EMG 45-RELS, with plug-in socket for cradle relay, size 2

Commercial data

Item number	2950802
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK6131
GTIN	4017918084141
Weight per piece (including packing)	104.62 g
Weight per piece (excluding packing)	104.62 g
Customs tariff number	85364900
Country of origin	DE

EMG 45-RELS/K2-W230 - Relay base



2950802

<https://www.phoenixcontact.com/us/products/2950802>

Technical data

Product properties

Product type	Relay socket
--------------	--------------

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Input data

Nominal input voltage U_N	230 V AC
	230 V AC

Connection data

Input side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Output side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Width	45 mm
Height	75 mm
Depth	82.5 mm

Material specifications

Color	green (RAL 6021)
Insulating material	PC-F

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

EMG 45-RELS/K2-W230 - Relay base



2950802

<https://www.phoenixcontact.com/us/products/2950802>

Standards and regulations

Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0109-11, draft
	DIN EN 50178/VDE 0160 (in relevant parts)

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

EMG 45-RELS/K2-W230 - Relay base



2950802

<https://www.phoenixcontact.com/us/products/2950802>

Drawings

Circuit diagram



EMG 45-RELS/K2-W230 - Relay base



2950802

<https://www.phoenixcontact.com/us/products/2950802>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com