

UM-H - Covering hood

2955441

<https://www.phoenixcontact.com/us/products/2955441>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Transparent hood, for one base element, UM-BEFE (with 2 UM-SE) snaps on, 60 mm wide, 50 mm high

The figure shows a combination of versions UM-SE-1, UM 16,5-1 BE, UM-BE 35-1, UM-BEFE 35-1, UM-SE-A 60-R and UM-A/U 73 CM

Commercial data

Item number	2955441
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDDZ
GTIN	4017918085513
Weight per piece (including packing)	24.65 g
Weight per piece (excluding packing)	24.05 g
Customs tariff number	85369010
Country of origin	PL

UM-H - Covering hood

2955441

<https://www.phoenixcontact.com/us/products/2955441>



Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM
Ventilation openings present	no

Dimensions

Width	60 mm
Height	50 mm
Depth	40 mm

Material specifications

Color (Covering hood)	transparent
Surface characteristics	untreated

UM-H - Covering hood

2955441

<https://www.phoenixcontact.com/us/products/2955441>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2955441>



UL Recognized

Approval ID: E240868

UM-H - Covering hood

2955441

<https://www.phoenixcontact.com/us/products/2955441>



Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-H - Covering hood



2955441

<https://www.phoenixcontact.com/us/products/2955441>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com