

# UMKS- 8 IM/LA/P - Termination board

2971616

<https://www.phoenixcontact.com/us/products/2971616>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, for mounting on NS 35/7.5 or NS 32, with LED for 8 p-n-p switching sensors

## Commercial data

Item number	2971616
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C422
Product key	DK2181
GTIN	4017918088477
Weight per piece (including packing)	194.7 g
Weight per piece (excluding packing)	150.94 g
Customs tariff number	85369010
Country of origin	DE

# UMKS- 8 IM/LA/P - Termination board



2971616

<https://www.phoenixcontact.com/us/products/2971616>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE

### Insulation characteristics

Overvoltage category	III
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	24 V DC
Max. current carrying capacity per branch	1 A

### Connection data

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Signaling

Status display present	yes
------------------------	-----

### Dimensions

#### Item dimensions

Width	67.5 mm
Height	77 mm
Depth	72 mm

### Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

### Standards and regulations

Standards/regulations	DIN VDE 0110
-----------------------	--------------

### Mounting

# UMKS- 8 IM/LA/P - Termination board



2971616

<https://www.phoenixcontact.com/us/products/2971616>

Mounting position	any
-------------------	-----

## Notes

Order information:	Version with light indicator: 24 V DC
Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

# UMKS- 8 IM/LA/P - Termination board




2971616

<https://www.phoenixcontact.com/us/products/2971616>

## Drawings

Circuit diagram



# UMKS- 8 IM/LA/P - Termination board



2971616

<https://www.phoenixcontact.com/us/products/2971616>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)