

UM-A/U73- 105 - Covering hood

2955645

<https://www.phoenixcontact.com/us/products/2955645>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Example photograph

U-shaped cover, transparent, 73 mm wide, can be screwed to side element UM-SE-A 73, for 3 UM-BE...35 base elements

Your advantages

- Tailor-made housing length, can be cut to length with millimeter precision
- Easy integration of large electronics components, thanks to the open design
- Heat-resistant UM-PRO made from polyamide with UL approval up to 100°C
- Easy device mounting thanks to snap-mount principle (the sides are fixed without the aid of tools)
- High degree of flexibility, thanks to freely positionable covering hoods

Commercial data

Item number	2955645
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDBZ
GTIN	4017918085612
Weight per piece (including packing)	73.82 g
Weight per piece (excluding packing)	61.13 g
Customs tariff number	39169010
Country of origin	DE

UM-A/U73- 105 - Covering hood

2955645

<https://www.phoenixcontact.com/us/products/2955645>



Technical data

Product properties

Product type	Component housing cover
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM AU
Ventilation openings present	no

Dimensions

Width	73 mm
-------	-------

Material specifications

Color (Covering hood)	transparent
Material	PC

UM-A/U73- 105 - Covering hood

2955645

<https://www.phoenixcontact.com/us/products/2955645>



Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM-A/U73- 105 - Covering hood



2955645

<https://www.phoenixcontact.com/us/products/2955645>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.494 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com