

UM 72-LG 10 BK - Lateral element



2977513

<https://www.phoenixcontact.com/us/products/2977513>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile housing and board base, 10 mm wide module, consisting of two side elements



Commercial data

Item number	2977513
Packing unit	10 pc
Minimum order quantity	100 pc
Note	Made to order (non-returnable)
Sales key	AC22
Product key	ACHDBA
GTIN	4017918281496
Weight per piece (including packing)	14 g
Weight per piece (excluding packing)	11 g
Customs tariff number	39269097
Country of origin	PL

UM 72-LG 10 BK - Lateral element

2977513

<https://www.phoenixcontact.com/us/products/2977513>




Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM72
Type	For PCB dimensions: 8 mm x 72 mm
Ventilation openings present	no

Dimensions

Dimensional drawing	
Width	8 mm
Length	72 mm

Material specifications

Color (Side element)	black (RAL 9005)
Material Lateral element	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

PCB data

Number of PCB holders	2
-----------------------	---

Mounting

Mounting type	DIN rail mounting, screw connection with extruded profile
---------------	---

UM 72-LG 10 BK - Lateral element


2977513

<https://www.phoenixcontact.com/us/products/2977513>



Drawings

Dimensional drawing



UM 72-LG 10 BK - Lateral element



2977513

<https://www.phoenixcontact.com/us/products/2977513>

Classifications

ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM 72-LG 10 BK - Lateral element



2977513

<https://www.phoenixcontact.com/us/products/2977513>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.1 Climate Change	
CO2e kg	0.078 kg CO2e

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com