

2988890

<https://www.phoenixcontact.com/us/products/2988890>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



WebVisit 5 is the engineering tool used to create web visualizations for all controllers with integrated web server. The Pro version includes functions such as alarm lists, trends, a user management feature, URL jumps, and other popular functions.

## Product description

In addition to the basic functions, the Pro version of WebVisit contains the following macros:

- User level management
- Pointer tool
- URL jumps
- Alarm generation
- Trending
- Animated GIFs

## Your advantages

- Macro library with functions such as alarm lists, trends, a user management feature, URL jumps, etc.
- Engineering tool used to create web visualizations for all controllers with integrated web server
- No programming knowledge is necessary for the creation of visualization pages
- The visualization pages are displayed in any standard browser

## Commercial data

Item number	2988890
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR13
Product key	DRDABA
GTIN	4046356177511
Weight per piece (including packing)	310.5 g
Weight per piece (excluding packing)	310.5 g
Customs tariff number	85234925
Country of origin	DE

2988890

<https://www.phoenixcontact.com/us/products/2988890>

## Technical data

### Product properties

Product type	Visualization
--------------	---------------

### System properties

Control system	(Target system) Embedded controller
Type of software	On-premises
Intended use for the software	Web editor

### License information

Type of license	Single-user license
	Freeware

### Functionality

Basic functions	The user interface has a functional design and even the basic version offers numerous graphic basic elements and functions.
	The variables needed for visualization are imported directly from PC Worx.
Control system	(Target system) Embedded controller
Associated hardware	Phoenix Contact control
Number of I/O nodes	128000

### System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® 10 (32-bit/64-bit), as of Build 1511
	Windows®11, as of Build 22000.675
Processor	min. Intel® Pentium® 4 / Celeron® 1,6 GHz
Hard disk memory	min. 2 GByte
Supported browsers	Internet Explorer Version 8 or later
Languages supported	English
Screen resolution	XGA (1024 x 768)

# WEBVISIT PRO - Visualization software



2988890

<https://www.phoenixcontact.com/us/products/2988890>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)