

UMK-BE 11,25 BK - Electronics housing



2976394

<https://www.phoenixcontact.com/us/products/2976394>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic board base, plug-in module base element

The figure shows a combination of versions UMK SE 11,25, UMK BE 11,25,- 22,5, - 45 and UMK-FE, in green

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2976394 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC13 |
| Product key | ACHDCA |
| GTIN | 4017918281199 |
| Weight per piece (including packing) | 4.42 g |
| Weight per piece (excluding packing) | 4.42 g |
| Customs tariff number | 85369085 |
| Country of origin | PL |

UMK-BE 11,25 BK - Electronics housing

2976394


<https://www.phoenixcontact.com/us/products/2976394>

Technical data

Product properties

| | |
|---------------------|---|
| Housing type | Panel mounting base |
| Type | Module width 11.25 mm, since the housing can remain open at the top, it is possible for parts to protrude above the actual profile height |
| Number of positions | 999 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 33.75 mm |
| Height NS 35/7,5 | 165 mm |
| Depth | 77 mm |
| Length | 77 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V2 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
|---------------------------------|-------------------|


UMK-BE 11,25 BK - Electronics housing



2976394

<https://www.phoenixcontact.com/us/products/2976394>

Drawings



UMK-BE 11,25 BK - Electronics housing



2976394

<https://www.phoenixcontact.com/us/products/2976394>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com