

# SD FLASH 256MB - Program/configuration memory



2988120

<https://www.phoenixcontact.com/us/products/2988120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Program and configuration memory, plug-in, 256 MB



Similar figure

## Product description

Program and configuration memory to save the application programs and other files in the file system of the PLC. Alternatively, a program and configuration memory with integrated license is available to disconnect various function blocks.

## Your advantages

- Program and configuration memory, plug-in
- For storing application programs and other files in the file system of the PLC

## Commercial data

Item number	2988120
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR10
Product key	DRAAZA
GTIN	4046356342360
Weight per piece (including packing)	9.2 g
Weight per piece (excluding packing)	8.5 g
Customs tariff number	85235110
Country of origin	TW

# SD FLASH 256MB - Program/configuration memory



2988120

<https://www.phoenixcontact.com/us/products/2988120>

## Technical data

### Product properties

Product type	Storage medium
Application	Program/configuration memory
Mounting position	vertical
Memory type	FLASH-EPROM
Memory size	256 Mbyte

### Electrical properties

Maximum power dissipation for nominal condition	0.165 W
---	---------

#### Supply

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC
Typical current consumption	typ. 50 mA

### Material specifications

Housing material	Plastic
------------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

### Mounting

Mounting position	vertical
-------------------	----------

# SD FLASH 256MB - Program/configuration memory



2988120

<https://www.phoenixcontact.com/us/products/2988120>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)