

# SB 4-8-T - Bridge bar

3026379

<https://www.phoenixcontact.com/us/products/3026379>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, pitch: 8.2 mm, number of positions: 4, color: orange



## Commercial data

Item number	3026379
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918351236
Weight per piece (including packing)	7.565 g
Weight per piece (excluding packing)	7.42 g
Customs tariff number	85369095
Country of origin	PL

# SB 4-8-T - Bridge bar



3026379

<https://www.phoenixcontact.com/us/products/3026379>

## Technical data

### Product properties

Product type	Bridge bar
Number of positions	4
Pitch	8.2 mm
Potentials	1

### Dimensions

Width	31.7 mm
Height	15.6 mm
Depth	15.6 mm
Pitch	8.2 mm

### Material specifications

Color	orange (RAL 2003)
Material	Copper
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Plug-in mounting
---------------	------------------

# SB 4-8-T - Bridge bar



3026379

<https://www.phoenixcontact.com/us/products/3026379>

## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 10.0	EC000489
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SB 4-8-T - Bridge bar



3026379

<https://www.phoenixcontact.com/us/products/3026379>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.069 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)