

FL MGUARD PCI/533 VPN - Router



2989417

<https://www.phoenixcontact.com/us/products/2989417>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Firewall/router in the PCI format 533 MHz processor cycle frequency and VPN



Commercial data

Item number	2989417
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DNN332
GTIN	4046356298926
Weight per piece (including packing)	114 g
Weight per piece (excluding packing)	117 g
Customs tariff number	85176200
Country of origin	DE

Technical data

Interfaces

Ethernet

Connection method	RJ45
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Signal LEDs	WAN link, WAN activity, LAN link, LAN activity
No. of channels	2

System properties

Functionality

Basic functions	Firewall/Router
-----------------	-----------------

System requirements

Supported browsers	HTTPS support required
--------------------	------------------------

Product properties

Product type	Security routers without DIN rail mounting
Format	PCI

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Electrical properties

Power consumption	max. 2.5 W
Local diagnostics	One LED per port Activity LED red
	One LED per port Link active Green LED

Supply

Power supply connection	Via PCI bus
-------------------------	-------------

Connection data

Connection method	RJ45, shielded
-------------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	0 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 % (non-condensing)

Mounting

Mounting type	PCI slot
---------------	----------

FL MGuard PCI/533 VPN - Router



2989417

<https://www.phoenixcontact.com/us/products/2989417>

EMC data

Electromagnetic compatibility

Conformance with EMC Directive 2004/108/EC

Signaling

Status display

Link/activity per port

FL MGUARD PCI/533 VPN - Router



2989417

<https://www.phoenixcontact.com/us/products/2989417>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com