

# PSBJ 3/52/6 GY - Test plug strip



3048085

<https://www.phoenixcontact.com/us/products/3048085>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, number of positions: 1, color: gray

## Your advantages

- The test socket PSBJ... is used in place of the normal bridge screw and ensures the voltage pick-off on a bridged group of terminals
- The test sockets are tailored to the special applications encountered in the power supply industry

## Commercial data

Item number	3048085
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918880989
Weight per piece (including packing)	6.55 g
Weight per piece (excluding packing)	6.49 g
Customs tariff number	85366990
Country of origin	PL

# PSBJ 3/52/6 GY - Test plug strip



3048085

<https://www.phoenixcontact.com/us/products/3048085>

## Technical data


### Product properties

Product type	Test socket
Number of positions	1

### Connection data

Test socket torque	M3
Connection method	Screw connection

### Dimensions

Dimensional drawing	
Width	6 mm
Pin diameter	4 mm
Screw thread	M3

### Material specifications

Color	gray
Material	Brass
Insulating material	PA
Contact material	PE-LD, silver-plated brass

### Mounting

Screw thread	M3
--------------	----


# PSBJ 3/52/6 GY - Test plug strip

3048085

<https://www.phoenixcontact.com/us/products/3048085>

## Drawings

Dimensional drawing



# PSBJ 3/52/6 GY - Test plug strip

3048085

<https://www.phoenixcontact.com/us/products/3048085>



## Classifications

### UNSPSC

UNSPSC 21.0	39121410
-------------	----------

# PSBJ 3/52/6 GY - Test plug strip



3048085

<https://www.phoenixcontact.com/us/products/3048085>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)