

# W-RBO 10 - Washer

3049065

<https://www.phoenixcontact.com/us/products/3049065>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Washer, depth: 2 mm, height: 2 mm, diameter: 16 mm



## Commercial data

Item number	3049065
Packing unit	100 pc
Minimum order quantity	1,000 pc
Product key	BE4ZWX
GTIN	4055626228174
Weight per piece (including packing)	1.2 g
Weight per piece (excluding packing)	1.101 g
Country of origin	IN

# W-RBO 10 - Washer

3049065

<https://www.phoenixcontact.com/us/products/3049065>



## Technical data

### Product properties

Product type	Mounting material
--------------	-------------------

### Dimensions

Height	2 mm
Depth	2 mm
Diameter	16 mm

### Internal dimensions

Internal diameter	10.5 mm
-------------------	---------

### Material specifications

Material	Steel
Coating	zinc plating

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# W-RBO 10 - Washer

3049065

<https://www.phoenixcontact.com/us/products/3049065>



## Classifications

### ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

### ETIM

ETIM 10.0	EC002848
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# W-RBO 10 - Washer



3049065

<https://www.phoenixcontact.com/us/products/3049065>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)