

# HV M8/1-VS 2 - Connection element



3049369

<https://www.phoenixcontact.com/us/products/3049369>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection element, depth: 4 mm, width: 20 mm, height: 41 mm, number of positions: 2, color: silver-colored

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3049369       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BE49          |
| Product key                          | BE4Z2X        |
| GTIN                                 | 4046356313681 |
| Weight per piece (including packing) | 24.83 g       |
| Weight per piece (excluding packing) | 24.77 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | CN            |

# HV M8/1-VS 2 - Connection element



3049369

<https://www.phoenixcontact.com/us/products/3049369>

## Technical data

### Product properties

|                     |        |
|---------------------|--------|
| Product type        | Bridge |
| Number of positions | 2      |

### Connection data

|                      |       |
|----------------------|-------|
| Maximum load current | 150 A |
|----------------------|-------|

### Dimensions

|                    |        |
|--------------------|--------|
| Width              | 20 mm  |
| Height             | 41 mm  |
| Depth              | 4 mm   |
| Drill hole spacing | 23 mm  |
| Hole diameter      | 8.6 mm |

### Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Copper         |

### Mechanical properties

#### Technical data

|                    |       |
|--------------------|-------|
| Drill hole spacing | 23 mm |
|--------------------|-------|

# HV M8/1-VS 2 - Connection element



3049369

<https://www.phoenixcontact.com/us/products/3049369>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27141190 |
| ECLASS-15.0 | 27250190 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002848 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# HV M8/1-VS 2 - Connection element



3049369

<https://www.phoenixcontact.com/us/products/3049369>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)