

HV M5/1-VS 3 - Connection element



3049440

<https://www.phoenixcontact.com/us/products/3049440>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection element, depth: 4 mm, width: 12 mm, height: 42 mm, number of positions: 3, color: silver-colored

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3049440 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE49 |
| Product key | BE4Z2X |
| GTIN | 4046356313551 |
| Weight per piece (including packing) | 15.79 g |
| Weight per piece (excluding packing) | 15.3 g |
| Customs tariff number | 85369010 |
| Country of origin | CN |

HV M5/1-VS 3 - Connection element



3049440

<https://www.phoenixcontact.com/us/products/3049440>

Technical data

Product properties

| | |
|---------------------|--------|
| Product type | Bridge |
| Number of positions | 3 |

Connection data

| | |
|----------------------|------|
| Maximum load current | 76 A |
|----------------------|------|

Dimensions

| | |
|--------------------|--------|
| Width | 12 mm |
| Height | 42 mm |
| Depth | 4 mm |
| Drill hole spacing | 15 mm |
| Hole diameter | 5.6 mm |

Material specifications

| | |
|----------|----------------|
| Color | silver-colored |
| Material | Copper |

Mechanical properties

Technical data

| | |
|--------------------|-------|
| Drill hole spacing | 15 mm |
|--------------------|-------|

HV M5/1-VS 3 - Connection element



3049440

<https://www.phoenixcontact.com/us/products/3049440>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141190 |
| ECLASS-15.0 | 27250190 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002848 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

HV M5/1-VS 3 - Connection element



3049440

<https://www.phoenixcontact.com/us/products/3049440>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com