

UEGM 25 BU - Electronics housing

3016088

<https://www.phoenixcontact.com/us/products/3016088>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronics housing, color: blue ,Component housing, without vents, Complete housing, cross connection: Not provided for

The figure shows version UEGM 22.5

Commercial data

Item number	3016088
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	ACHCCB
GTIN	4017918282707
Weight per piece (including packing)	55.75 g
Weight per piece (excluding packing)	47.638 g
Country of origin	DE

3016088

<https://www.phoenixcontact.com/us/products/3016088>

Technical data

Product properties

Product type	Complete housing
Housing type	Component housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM 25
Type	Connection system integrated, housing closed
Number of positions	6
Number of rows	1
Ventilation openings present	no

Material specifications

Color (Housing)	blue (RAL 5015)
Material Housing	PA
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

UEGM 25 BU - Electronics housing





3016088

<https://www.phoenixcontact.com/us/products/3016088>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3016088>

 cULus Recognized Approval ID: E60425-19770427				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	10 A	30 - 12	-

 UL Recognized Approval ID: E240868				
--------------------------------------------------------------------------------------------------------------------------------	--	--	--	--

UEGM 25 BU - Electronics housing



3016088

<https://www.phoenixcontact.com/us/products/3016088>

Classifications

ECLASS

ECLASS-13.0	27190501
ECLASS-15.0	27190501

ETIM

ETIM 10.0	EC001031
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UEGM 25 BU - Electronics housing



3016088

<https://www.phoenixcontact.com/us/products/3016088>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.328 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com