

KDT 6-7 - Cable sleeve

3063141

<https://www.phoenixcontact.com/us/products/3063141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Small, slotted cable sleeves suitable for conductors with a diameter of 6-7 mm.



Product description

Slotted sleeves for accommodating preassembled cables and lines of 6 mm ... 7 mm diameter, can be used in the KEL sealing frames: KEL 16/4, KEL 16/8, KEL 24/4, KEL 24/5, KEL 24/7, KEL 24/10. When mounted, the sleeves simultaneously function as strain relief according to DIN EN 50262.

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 3063141 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | AF7CCX |
| GTIN | 4046356300926 |
| Weight per piece (including packing) | 7.8 g |
| Weight per piece (excluding packing) | 7.8 g |
| Customs tariff number | 40169300 |
| Country of origin | DE |

KDT 6-7 - Cable sleeve



3063141

<https://www.phoenixcontact.com/us/products/3063141>

Technical data

Product properties

| | |
|-------------------|--------------|
| Product type | Cable sleeve |
| No. of conductors | 1 |

Material specifications

| | |
|--|-----------|
| Material | Elastomer |
| Flammability rating according to UL 94 | V0 |

Cable/line

| | |
|-------------------------|---------------|
| External cable diameter | 6 mm ... 7 mm |
|-------------------------|---------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP54 |
| Ambient temperature (operation) | -20 °C ... 80 °C |

KDT 6-7 - Cable sleeve

3063141

<https://www.phoenixcontact.com/us/products/3063141>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27144425 |
| ECLASS-15.0 | 27144425 |

KDT 6-7 - Cable sleeve

3063141

<https://www.phoenixcontact.com/us/products/3063141>



Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com