

PS-3,5/E - Test plug



3031012

<https://www.phoenixcontact.com/us/products/3031012>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, Individual test plug, number of positions: 1, color: red

Your advantages

- The test plugs make contact in the function shaft of terminal blocks from the CLIPLINE complete system

Commercial data

Item number	3031012
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4055626167572
Weight per piece (including packing)	1.75 g
Weight per piece (excluding packing)	1.73 g
Customs tariff number	85366990
Country of origin	PL

PS-3,5/E - Test plug



3031012

<https://www.phoenixcontact.com/us/products/3031012>

Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1
Potentials	1

Electrical properties

Maximum load current	2 A
Max. voltage	250 V

Connection data

Maximum load current	2 A
Connection method	Push-in connection
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²

Dimensions

Width	3.5 mm
Height	15.9 mm
Depth	43.3 mm

Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

PS-3,5/E - Test plug



3031012

<https://www.phoenixcontact.com/us/products/3031012>

Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

ETIM

ETIM 10.0	EC002555
-----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PS-3,5/E - Test plug



3031012

<https://www.phoenixcontact.com/us/products/3031012>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com